



FEATURES

- 1030 nm, 1053 nm, 1064 nm
- Dynamic Extinction Ratio up to 55 dB

APPLICATIONS

- Inertial confinement fusion
- Interaction of intense light with matter
- Laser Plasma interaction
- Laser implosion

OPTIONS

- Other maximum Extinction Ration value
- Wavelength

RELATED EQUIPMENTS

- ModBox-Pulse-Shaper
- Front-End System

The ModBox-DER is the first equipment specially designed to measure the Dynamic Extinction Ratio (DER) of high contrast ns optical pulses in the 1000 nm wavelength band. It measures Extinction Ratios up to more than 50 dB, for pulses as short as 5 ns, from single-shot operation to 10 kHz repetition frequency.

The ModBox-DER uses the French Nuclear Agency technology developed for the monitoring of the MegaJoule laser. It finds applications mostly in ultra-intense laser facilities.

Principle

The high contrast pulse to be characterized is split in two parts: one part is strongly attenuated by a factor which is typically the expected value of the DER; for the second part, most of the pulse is retrieved using a high extinction modulator, leaving only the pedestal. The two parts are then measured with the same high bandwidth - high sensitivity photodetector for which only a few dB of dynamic range are required.

The main advantage of this measurement principle is the "self-calibration". Peak and noise powers of the optical pulse are measured by the same high bandwidth and high sensitivity photodetector.

Performances

Parameter	Min	Typ	Max	Unit
Input Signal				
Wavelength	1030 nm, 1053 nm, 1064 nm			-
Signal type	Optical Pulse			-
Pulse Width	5	-	25	ns
Pulse Rate	Single shot	-	10	kHz
Pulse amplitude	70	-	450	mW
Optical Characteristics				
DER	Automatic measurement			-
	10	50	55	dB
DER monitoring	-	until 1 week	-	-
Resolution	-	0.6	-	ns
Measuring window	500 n	-	2 m	s
Pulse acquisition rate	-	0.5	-	Hz


Ordering Information:




800 Village Walk #316
Guilford, CT 06437
Ph: 203-401-8093

Email orders to: sales@xsoptix.com
Fax orders to: 800-878-7282

Pulse and Pedestal Measurement



DER monitoring



Interfaces

Parameter	Symbol	Min	Max	Unit
Connectivity	Standard USB 2.0 Mouse / Keyboard / USB Key			
	Ethernet port (remote control)			
Operating System	Windows 7			
Display	8.1 inch touch display			

Ordering information

ModBox-DER-XXnm-YY-ZZ

DER = Dynamic Extinction Ratio
 XXnm = 1030nm, 1053nm, 1064nm
 YY = Optical Input Connector, FA : FC/APC - FC : FC/UPC - SC : SC/UPC
 ZZ = Optical Diagnostic Connector, FA : FC/APC - FC : FC/UPC - SC : SC/UPC

About us

ixBlue Photonics includes ixBlue ixFiber brand that produces specialty optical fibers and Bragg gratings based fiber optics components and ixBlue Photline brand that provides optical modulation solutions based on the company lithium niobate (LiNbO₃) modulators and RF electronic modules.

ixBlue Photonics serves a wide range of industries: sensing and instruments, defense, telecommunications, space and fiber lasers as well as research laboratories all over the world.

3, rue Sophie Germain
 25 000 Besançon - FRANCE
 Tel. : +33 (0) 381 853 180 - Fax : + 33 (0) 381 811 557

ixblue reserves the right to change, at any time and without notice, the specifications, design, function or form of its products described herein. All statements, specification, technical information related to the products herein are given in good faith and based upon information believed to be reliable and accurate at the moment of printing. However the accuracy and completeness thereof is not guaranteed. No liability is assumed for any inaccuracies and as a result of use of the products. The user must validate all parameters for each application before use and he assumes all risks in connection with the use of the products